

# Lightning Enterprises

Serious Equipment - Better Hearing Service

## PRODUCT INFORMATION:

### My Vac

*Personal Hearing Aid Cleaning System*

## SPECIFICATIONS:

Power Requirements :  
12V DC  
200 ma

Length: 5.25 inches  
Width: 3.25 inches  
Height: 1.75 inches  
Weight: 2 lbs  
Material: ABS plastic  
Color: Black  
Vacuum Capacity: 12" Hg  
Flow: 1.5 lpm



## My Vac

*Personal Hearing Aid Cleaning System*

Cerumen and debris accumulating in the sound outlet port is by far the #1 cause of poor hearing aid performance. Symptoms can include distorted, weak or no sound, and quite often can mean complete instrument failure. And the traditional tools given to the consumer for maintaining their hearing aids just don't go far enough to provide adequate debris removal. **My Vac** Personal Hearing Aid Cleaning System uses a vacuum pump which extracts and removes wax and debris, effectively cleaning the sound port and prolonging the life of the hearing aid. **My Vac** is a completely self contained unit, and includes a filter probe for easy wax removal, convenient storage clip, and blower port for removing clogs and obstructions in the tip. The probe tip can be easily removed for cleaning or replacement.

### Features include:

- \* Quality vacuum pump
- \* Filter Probe
- \* Probe storage clip
- \* Replaceable Filter
- \* Blower port for clearing probe
- \* 1 year warranty

## My Vac Pricing

**\$115.00**

### My Vac Slip-Luer Needle Packet Option

Slip-Luer which snaps onto the filter and includes 3 different needle tips for cleaning various parts of the hearing aid, including inside the sound port. Care should be taken when using needle tips as damage to the hearing aid could result.

My Vac Slip-Luer-Needle Packet: \$4.95 ea

Lightning Enterprises  
18 Harlan Drive • Limington, ME 04049  
Toll Free: 877-546-1797  
[www.lightning-enterprises.com](http://www.lightning-enterprises.com)